



Vertical Lift, High Traffic Areas



Minimizing Vertical Lift Storage Profile

For VL Series to remain less than 4" (102 mm)* from the wall* when in storage position, follow these guidelines:

1. Monitor must not be more than 2-1/2" (63 mm) thick.
2. Keyboard should not be more than 7-1/4" (184 mm) deep.
3. Dimension "A" must be no greater than 8-3/4" (222 mm).
4. Use Standard Keyboard Tray option only (Slide-Out Keyboard Tray option depth $\geq$ 4-1/2", 114 mm).

* Exceptions: If you want to install your keyboard in a forward position while remaining $\leq$ 4" (102 mm) from the wall, "A" $\leq$ 7" (178 mm). See Figure 1.

If you want to use a keyboard wrist rest, dimension "A" can be calculated by adding 3-1/2" (89 mm) to the keyboard depth "B" and subtracting this sum from 16-1/2" (419 mm). See Figure 2.




Fig. 1





Fig. 2



$$A = 16.5 - (B + 3.5)$$

B = Keyboard Depth

Americas Sales and Corporate Headquarters

St. Paul, MN USA
(800) 888-8458
+1-651-681-7600
www.ergotron.com
sales@ergotron.com

EMEA Sales

Amersfoort, The Netherlands
+31 33 45 45 600
www.ergotron.com
info.eu@ergotron.com

APAC Sale

Tokyo, Japan
www.ergotron.com
apaccustomerservice@ergotron.com

Worldwide OEM Sales

www.ergotron.com
info.oem@ergotron.com

